

# X ULTRA 3

## L40286200 Phantom/Black/Hawaiian

Phantom/Black/Hawaiian



**advanced chassis**  
**sensiFIT**



**This hiking shoe is easy on the way up, even better on the way down.**

A best seller, the X ULTRA 3 has evolved into an even more effective hiking shoe. Thanks to Descent Control technology, it efficiently tackles technical hikes and really shines during tough descents. Wear this breathable pair in warm weather and dirt conditions, and head downhill with a spring in your step.

### **Foothold**

A refined last works with the reinforced top arm of the sensifit, holding your foot comfortably in place, especially moving downhill.

### **Stability and cushioning**

The Advanced Chassis, surrounded by foam cushioning for comfort, connects directly to the sole to stabilize your heel.

### **Grip**

Two different types of rubber result in better grip. A patterned area on the heel grabs terrain more aggressively, giving you more control especially on descents.

- Breathability : 6/6
- Lightness : 4/6
- Protection : 5/6
- Stability : 6/6
- Drop (in mm) : 11
- Midsole heel height (mm) : 19
- Midsole toe height (mm) : 8
- Weight (g) : 365

### **OUTSOLE**

- Chevron lugs
- Contagrip® TD

**MIDSOLE**

- EnergyCell

**CHASSIS**

- Advanced Chassis™

**UPPER MATERIAL**

- Anti-debris Mesh
- Synthetic upper

**LINING MATERIAL**

- Mesh and textile lining

**SOCKLINER**

- Molded OrthoLite®

**UPPER CONSTRUCTION**

- Lace pocket
- Protective toecap
- SensiFit™
- Welded upper

**LACING SYSTEM**

- Quicklace™

| Size info |     |           |           |      |           |           |     |           |           |      |           |           |      |           |
|-----------|-----|-----------|-----------|------|-----------|-----------|-----|-----------|-----------|------|-----------|-----------|------|-----------|
| D         | 40  | 40<br>2/3 | 41<br>1/3 | 42   | 42<br>2/3 | 43<br>1/3 | 44  | 44<br>2/3 | 45<br>1/3 | 46   | 46<br>2/3 | 47<br>1/3 | 48   | 49<br>1/3 |
| F         | 40  | 40<br>2/3 | 41<br>1/3 | 42   | 42<br>2/3 | 43<br>1/3 | 44  | 44<br>2/3 | 45<br>1/3 | 46   | 46<br>2/3 | 47<br>1/3 | 48   | 49<br>1/3 |
| JP        | 25  | 25.5      | 26        | 26.5 | 27        | 27.5      | 28  | 28.5      | 29        | 29.5 | 30        | 30.5      | 31   | 32        |
| MON<br>DO | 25  | 25.5      | 26        | 26.5 | 27        |           | 28  | 28.5      | 29        | 29.5 | 30        | 30.5      | 31   | 32        |
| UK        | 6.5 | 7         | 7.5       | 8    | 8.5       | 9         | 9.5 | 10        | 10.5      | 11   | 11.5      | 12        | 12.5 | 13.5      |
| US        | 7   | 7.5       | 8         | 8.5  | 9         | 9.5       | 10  | 10.5      | 11        | 11.5 | 12        | 12.5      | 13   | 14        |

The picture displayed is taken on a salesman sample.